

Split Spherical Roller Bearing Interchanges & Accessories

222 Series — SAF500 Housings

Solid SRB with Tapered Bore	INCH				METRIC			Housing
	Shaft Dia.	Split SRB	Split Labyrinth Seal	Split SuperTAC II	Shaft Dia.	Split SRB*	Split Labyrinth Seal	SAF500
22213..K	2-3/16	222S.203	LEERS29X0203-N	TAS29X0203	60	222SM60	LEERS35XM60-S	SAF513X0203U
22215..K	2-7/16	222S.207	LEERS37X0207-N	TAS37X0207	65	222SM65	LEERS40XM65-S	SAF515X0207U
22215..K	2-1/2	222S.208	LEERS38X0208-S	N/A	65	222SM65	LEERS40XM65-S	SAF515X0207U
22216..K	2-11/16	222S.211	LEERS44X0211-N	TAS44X0211	70	222SM70	LEERS45XM70-S	SAF516X0211U
22217..K	2-15/16	222S.215	LEERS53X0215-N	TAS53X0215	75	222SM75	LEERS53XM75-S	SAF517X0215U
22217..K	3	222S.300	LEERS54X0300-N	TAS54X0300	75	222SM75	LEERS53XM75-S	SAF517X0215U
22218..K	3-3/16	222S.303	LEERS69X0303-N	TAS188X0303	80	222SM80	LEERS188XM80-S	SAF518X0303U
22220..K	3-7/16	222S.307	LEERS102X0307-N	TAS102X0307	90	222SM90	LEERS102XM90-N	SAF520X0307U
22220..K	3-1/2	222S.308	LEERS103X0308-N	N/A	90	222SM90	LEERS102XM90-N	SAF520X0307U
22222..K	3-15/16	222S.315	LEERS109X0315-N	TAS109X0315	100	222SM100	LEERS109XM100-N	SAF522X0315U
22222..K	4	222S.400	LEERS110X0400-N	TAS110X0400	100	222SM100	LEERS109XM100-N	SAF522X0315U
22224..K	4-3/16	222S.403	LEERS113X0403-N	TAS113X0403	110	222SM110	LEERS113XM110-S	SAF524X0403U
22226..K	4-7/16	222S.407	LEERS117X0407-N	TAS117X0407	115	222SM115	LEERS118XM115-S	SAF526X0407U
22226..K	4-1/2	222S.408	LEERS118X0408-N	TAS118X0408	115	222SM115	LEERS118XM115-S	SAF526X0407U
22228..K	4-15/16	222S.415	LEERS122X0415-N	TAS122X0415	125	222SM125	LEERS122XM125-N	SAF528X0415U
22228..K	5	222S.500	LEERS123X0500-N	TAS123X0500	125	222SM125	LEERS122XM125-N	SAF528X0415U
22230..K	5-3/16	222S.503	LEERS125X0503-N	TAS125X0503	135	222SM135	LEERS126XM135-S	SAF530X0503U
22232..K	5-7/16	222S.507	LEERS130X0507-N	TAS130X0507	140	222SM140	LEERS131XM140-S	SAF532X0507U
22234..K	5-15/16	222S.515	LEERS140X0515-N	TAS140X0515	150	222SM150	LEERS140XM150-S	SAF534X0515U
22234..K	6	222S.600	LEERS141X0600-N	TAS141X0600	150	222SM150	LEERS140XM150-S	SAF534X0515U
22236..K	6-7/16	222S.607	LEERS148X0607-N	TAS148X0607	160	222SM160	LEERS148XM160-S	SAF536X0607U
22236..K	6-1/2	222S.608	LEERS149X0608-N	TAS149X0608	160	222SM160	LEERS148XM160-S	SAF536X0607U
22238..K	6-15/16	222S.615	LEERS155X0615-N	TAS155X0615	170	222SM170	LEERS155XM170-N	SAF538X0615U
22238..K	7	222S.700	LEERS156X0700-N	TAS156X0700	170	222SM170	LEERS155XM170-N	SAF538X0615U
22240..K	7-3/16	222S.703	LEERS159X0703-N	TAS159X0703	180	222SM180	LEERS159XM180-N	SAF540X0703U
22244..K	7-1/2	222S.708	LEERS162X0708-N	TAS162X0708	200	222SM200	LEERS167XM200-S	SAF544X0715U
22244..K	7-15/16	222S.715	LEERS167X0715-N	TAS167X0715	200	222SM200	LEERS167XM200-S	SAF544X0715U
22244..K	8	222S.800	LEERS168X0800-N	TAS168X0800	200	222SM200	LEERS167XM200-S	SAF544X0715U

The split SRB replaces the solid SRB with tapered bore and the adapter sleeve
Some split seals upon request

*Metric Ø60 and Ø110 need special housing



FAG Split Spherical Roller Bearings Easy on, easy off means less downtime!

Instead of using traditional solid bearings that require complicated and time-consuming replacement procedures – such as pulling gears and couplings, dismantling drives and stripping line shafting – consider FAG split spherical roller bearings from Schaeffler.

Their inner ring, outer ring and cage assembly are split into halves for easy mounting and dismounting. Easy on, easy off means less downtime.

Cost comparison: standard vs. split bearing

