

SAF500 Housings & Accessories: Universal/Standard

		SAF500 Housings				Included in Universal Housing			SRB and Adapter		Taconite
Housing Size	Shaft Diameter	Gray Cast Iron		Ductile Cast Iron		Labyrinth Seal	End Cover	Stabilizing Ring	SRB	Adapter Sleeve	SuperTAC II
		Two-bolt	Four-bolt	Two-bolt	Four-bolt						
509	1-7/16	*		SAFD509X0107U		LER17X0107-G-A	EC509-R	SR-9-9	22209..-K	SNW09X0107	TA17X0107
510	1-11/16	*		SAFD510X0111U		LER20X0111-G-A	EC510-R	SR-10-10	22210..-K	SNW10X0111	TA20X0111
511	1-15/16	*		SAFD511X0115U		LER24X0115-G-A	EC511-R	SR-11-0	22211..-K	SNW11X0115	TA24X0115
513	2-3/16	*		SAFD513X0203U		LER29X0203-G-A	EC513-R	SR-13-0	22213..-K	SNW13X0203	TA29X0203
515	2-7/16	SAF515X0207U	FSAF515X0207U	SAFD515X0207U	FSAFD515X0207U	LER37X0207-G-A	EC515-R	SR-15-0	22215..-K	SNW15X0207	TA37X0207
516	2-11/16	*	*	SAFD516X0211U	FSAFD516X0211U	LER44X0211-G-A	EC516-R	SR-16-13	22216..-K	SNW16X0211	TA44X0211
517	2-15/16	SAF517X0215U	FSAF517X0215U	SAFD517X0215U	FSAFD517X0215U	LER53X0215-G-A	EC517-R	SR-17-14	22217..-K	SNW17X0215	TA53X0215
518	3-3/16	SAF518X0303U	FSAF518X0303U	SAFD518X0303U	FSAFD518X0303U	LER188X0303-G-A	EC518-R	SR-18-15	22218..-K	SNW18X0303	TA188X0303
520	3-7/16	SAF520X0307U	FSAF520X0307U	SAFD520X0307U	FSAFD520X0307U	LER102X0307-G-A	EC520-R	SR-20-17	22220..-K	SNW20X0307	TA102X0307
522	3-15/16		SAF522X0315U		SAFD522X0315U	LER109X0315-G-A	EC522-R	SR-22-19	22222..-K	SNW22X0315	TA109X0315
524	4-3/16		SAF524X0403U		SAFD524X0403U	LER113X0403-G-A	EC524-R	SR-24-20	22224..-K	SNW24X0403	TA113X0403
526	4-7/16		SAF526X0407U		SAFD526X0407U	LER117X0407-G-A	EC526-R	SR-26-0	22226..-K	SNW26X0407	TA117X0407
528	4-15/16		SAF528X0415U		SAFD528X0415U	LER122X0415-G-A	EC528-R	SR-28-0	22228..-K	SNW28X0415	TA122X0415
530	5-3/16		*		SAFD530X0503U	LER125X0503-G-A	EC530-R	SR-30-0	22230..-K	SNW30X0503	TA125X0503
532	5-7/16		SAF532X0507U		SAFD532X0507U	LER130X0507-G-A	EC532-R	SR-32-0	22232..-K	SNW32X0507	TA130X0507
534	5-15/16		SAF534X0515U		SAFD534X0515U	LER140X0515-G-A	EC534-R	SR-34-0	22234..-K	SNW34X0515	TA140X0515
536	6-7/16		SAF536X0607U		SAFD536X0607U	LER148X0607-G-A	EC536-R	SR-36-30	22236..-K	SNW36X0607	TA148X0607
538	6-15/16		SAF538X0615U		SAFD538X0615U	LER155X0615-G-A	EC538-R	SR-38-32	22238..-K	SNW38X0615	TA155X0615
540	7-3/16		*		SAFD540X0703U	LER159X0703-G-A	EC540-R	SR-40-34	22240..-K	SNW40X0703	TA159X0703
544	7-15/16		SAF544X0715U		SAFD544X0715U	LER167X0715-G-A	EC544-R	SR-44-38	22244..-K	SNW44X0715	TA167X0715

* Sizes will be available in ductile material only

SAF500 Housings & Accessories: Alternatives

Housing Size	Shaft Diameter	Alternatives Inch			Inch Shaft / Metric Threads	Shaft Diameter	Alternatives Metric			
	Inch	Split SRB	Split Labyrinth Seal	Split SuperTAC II	Adapter Sleeve	Metric mm	Labyrinth Seal*	Adapter Sleeve	Split SRB	Split Labyrinth Seal*
509	1-7/16				H309X107	40		H309		
510	1-11/16				H310X111	45		H310		
511	1-15/16				H311X115	50	LER24XM50-A	H311		
513	2-3/16	222S.203	LERS29X0203-N	TAS29X0203	H313X203	60	**			
515	2-7/16	222S.207	LERS37X0207-N	TAS37X0207	H315X207	65	LER44XM65-A	H315	222SM65	
516	2-11/16	222S.211	LERS44X0211-N	TAS44X0211	H316X211	70	LER45XM70-A	H316	222SM70	LERS45XM70
517	2-15/16	222S.215	LERS53X0215-N	TAS53X0215	H317X215	75	LER53XM75-A	H317	222SM75	LERS53XM75
518	3-3/16	222S.303	LERS69X0303-N	TAS188X0303	H318X303	80	LER188XM80-A	H318	222SM80	LERS188XM80
520	3-7/16	222S.307	LERS102X0307-N	TAS102X0307	H320X307	90	LER102XM90-A	H320	222SM90	LERS102XM90
522	3-15/16	222S.315	LERS109X0315-N	TAS109X0315	H322X315	100	LER109XM100-A	H322	222SM100	LERS109XM100
524	4-3/16	222S.403	LERS113X0403-N	TAS113X0403	H3124X403	110	**			
526	4-7/16	222S.407	LERS117X0407-N	TAS117X0407	H3126X407	115	LER118XM115-A	H3126	222SM115	LERS118XM115
528	4-15/16	222S.415	LERS122X0415-N	TAS122X0415	H3128X415	125	LER122XM125-A	H3128	222SM125	LERS122XM125
530	5-3/16	222S.503	LERS125X0503-N	TAS125X0503	H3130X503	135	LER126XM135-A	H3130	222SM135	LERS126XM135
532	5-7/16	222S.507	LERS130X0507-N	TAS130X0507	H3132X507	140	LER130XM140-A	H3132	222SM140	LERS131XM140
534	5-15/16	222S.515	LERS140X0515-N	TAS140X0515	H3134X515	150	LER140XM150-A	H3134	222SM150	LERS140XM150
536	6-7/16	222S.607	LERS148X0607-N	TA1548X0607	H3136X607	160	LER148XM160-A	H3136	222SM160	LERS148XM160
538	6-15/16	222S.615	LERS155X0615-N	TAS155X0615	H3138X615	170	LER155XM170-A	H3138	222SM170	LERS155XM170
540	7-3/16	222S.703	LERS159X0703-N	TAS159X0703	H3140X703	180	LER159XM180-A	H3140	222SM180	LERS159XM180
544	7-15/16	222S.715	LERS167X0715-N	TAS167X0715	H3144XX715	200	LER167XM200-A	H3144X	222SM200	LERS167XM200

* Some metric labyrinth seals upon request

** Split 60 and 110 need special housing

SCHAEFFLER